


# Mobile Contamination Characterization Center (MC<sup>3</sup>)



You are familiar with Einstein's Theory of Relativity:  $E = mc^2$ . Now UniTech brings relativity to Population Monitoring for Radiological Emergency Response:

Comparison	Current Technology	MC <sup>3</sup>
Dedicated technical staff member required for each member of the public to be monitored	Yes	No
Time required per person monitored	3 to 5 minutes	15 seconds
Monitoring capacity (persons / hour)	12 - 20	240 (single PM)
Number of probes	1	29
Probe area (square inches)	2 - 16	64
Effective area monitored (square inches per 5 second count period)	10 - 40	1856

## Preparedness = Mobile Contamination Characterization Center (P = MC<sup>3</sup>)

**The problem:** In a nuclear terrorist scenario – for example, the detonation of a Radiological Dispersion Device (RDD, aka Dirty Bomb) or Improvised Nuclear Device (IND) – there will be tens to hundreds of thousands of individuals evacuating the event epicenter.

- Emergency responders want the evacuation to minimize the spread of contamination, demanding a quarantined perimeter
- Population must be individually monitored for radiological contamination at the perimeter then channeled appropriately for action
- Delays increase the amount of time radioactive material remains on people
- Danger of public hysteria and panic rises as the situation continues unresolved

Armed only with conventional instrumentation, today's radiological emergency responders would be faced with a daunting or impossible task to monitor, sort and clear population in response to terrorist scenarios involving nuclear materials.

**The solution:** Speed up and optimize population monitoring and radiological decontamination using MC<sup>3</sup> technology.



## Benefits of the P = MC<sup>3</sup> Solution



- Customized to either a single container or multiple container arrangement; can incorporate both whole-body monitoring equipment and decontamination showers
- Specialized, sensitive equipment
- Mobility: Completely mobile including truck, rail and vessel
- Helicopter deployment available in the optional intermodal container design
- Can be supplied with automated leveling devices for uneven surfaces
- Storage: Service options include maintenance of equipment in an ever-ready state
- Quick set-up: Delivered units can be operational in as little as two hours
- Flexible utility service connections adaptable to varied electrical, water supply and wastewater discharge modalities
- Optional modules incorporate capabilities for electrical generation, portable water supply and waste water filtration or retention
- Computerized data systems for individual tagging and tracking (by indelible stamp, RFID, bar code, bracelet, necklace or other means)
- Decontamination facilities incorporate paired, individual shower and dress stalls for private showering and subsequent donning of clean, uncontaminated clothing
- Air handling (HVAC) and filtration systems minimize potential for airborne contamination, facilitate radiological cleanliness and thus reduce downtime
- Health physics support, administrative and supply areas
- Workflow maximizes throughput and minimizes radiological hazards

**For more information, contact your UniTech account manager or our corporate office. See a brief capabilities video at [www.UniTechUS.com/MC3.shtml](http://www.UniTechUS.com/MC3.shtml).**

**Specifications PMAB: Mechanical:** 35"W x 40"D x 81"H approx. 800 lbs. • **Electrical:** 120 Volts AC, 60 Hz, 5 Amps • **Detectors:** 29 Model 9090, 410 cm<sup>2</sup>, window 0.85 mg/cm<sup>2</sup> • **Electronics:** System C96, PC-based, optically isolated • **Counting gas:** P-10 (10% methane, 90% argon) flow rate 0.5 scfh • **Alternate counting gas:** C-15 (15% CO<sub>2</sub>, 85% argon) • **Gas Flow Rate:** typical 0.5 scfh (0.25 lpm) • **Beta MDA:** ~4000 dpm Cs-137 at 4 second count time per side (in beta mode) • **Alpha MDA:** ~1000 dpm Am-241 at 4 second count time per side (in alpha mode). In alpha/beta mode the alpha and beta count occur sequentially automatically.

© 2011 UniTech Services Group  
Patent pending

## Available in Various Configurations



Units can be combined for additional throughput.

## Plant Locations

Springfield, Massachusetts  
Royersford, Pennsylvania  
Oak Ridge, Tennessee  
Barnwell, South Carolina  
Macon, Georgia  
Morris, Illinois  
Santa Fe, New Mexico  
Ontario, California  
Richland, Washington  
Laar, Germany  
Coevorden, Netherlands  
Oakdale, UK  
La Bouilladisse, France

UT-11-006



Certificate Number 968



Certificate Number 968

**ISO 9001 CERTIFIED**



A Subsidiary of UniFirst Corporation



Certificate Number 968

**ISO 14001 CERTIFIED**

**UniTech Corporate Headquarters**  
295 Parker Street • P.O. Box 51957 • Springfield, MA 01151  
Toll free: 800-344-3824 • Tel: 413-543-6911 • Fax 413-543-6989  
[www.UniTechUS.com](http://www.UniTechUS.com) • [www.shopunitech.com](http://www.shopunitech.com)